



ProCreate

Professional Sculptors Putty



Sandy Garrity

Stefan B. Niehues



Patrick Keith



Justice Joseph



Highly recommended for sculpting of master miniatures & custom jewelry. Formulated to achieve consistent, stunning professional results every time.



ProCreate

Professional Sculptors Putty

- No Shrinkage
- Very Easy to Smooth
- Easy Tooling - Less Sticky
- Holds Extremely Fine Detail
- Mixed Color: Gray
- Customizable Formula

Highly recommended for sculpting of master miniatures & custom jewelry. Formulated to achieve consistent, stunning professional results every time.

NET WT. 2.5 OZ. (70g)

What are sculptors from all over the world saying about ProCreate?

- ProCreate putty is softer so it is much easier to mix and blend in when adding to a cured surface.
- Holds detail throughout the cure - no more spending 20 minutes trying to keep an edge sharp till it cures.
- Very easy to push around and smooth.
- Neutral color allows for a better detail contrast and helps with spotting mistakes.
- Files and grinds very smooth with no rough edges so corrections are easier to do.
- Excellent self adhesion.
- Adheres to metal after cure, but does not stick to tools during cure.



Professional Sculptors Putty

Customizable formula – Work life, hardness and color may all be adjusted to achieve different effects as shown in the Mixing Chart below.

% Resin (white)	% Hardener (black)	24 Hour Hardness, Shore D (+/- 2)	Work Life, Minutes (75° F / 23° C)	Comments
40	60	55	180	Softer and more flexible, good for organic shapes. Color: dark gray
50	50	65	120	Harder and more rigid. Color: medium gray
60	40	75	90	Very hard and rigid. Good for machines and hard edges. Color: light gray

Note: All figures are approximate since cure can change depending on the ambient temperature and amount of putty mixed (See “Additional Curing Information” section).

To Use:

1. Cut - desired amount of each part.
2. Mix - two parts together with fingers until a uniform gray color is achieved
3. Apply - to surface and sculpt.
See chart for projected working time.

Manipulating Cure Time:

- Place the mixed ProCreate™ in the freezer to stop hardening.
- Place the mixed ProCreate™ under a warm lamp (95° F / 35° C max – oven recommended) to speed the hardening process.

Features and Benefits:

- Mixed Color: Gray
- No shrinkage
- Very easy to smooth
- Easy tooling and less sticky
- Holds Extremely Fine Detail
- Customizable Formula

Additional Curing Information:

- Thin sections will cure more slowly
- Thicker sections will cure faster
- Heat will cure the epoxy faster
- Cold will cause the epoxy to cure more slowly

